

nVent LENTON Interlok HYA15HT Grout Additive, hete temperatuur



The nVent LENTON HYA15LM Grout Additive, Hot Temperature is designed to be used in conjunction with nVent LENTON Interlok grout-fill couplers and nVent LENTON Interlok HY15LM Grout. The additive is used to increase working time of the grout during hot temperature applications which allows for a longer time window to place the grout into the Interlok couplers. This proprietary grout additive increases the maximum working temperature of HY15LM grout from 100 °F (38 °C) to 122 °F (50 °C).

KENMERKEN

Allows for hot temperature grouting

Increases grout working time in hot climates

Extends the construction season

For use in pump or gravity fill applications

SPECIFICATIES

Table 1/1

Catalogusnummer	Compressiesterkte	Bedrijfstemperatuur	Gewicht van de eenheid
HYA15HT	24.1 MPa @ 1 d, 110.3 MPa @ 28 d	21 to 50 °C	0.05 kg

AANVULLENDE PRODUCTGEGEVENS

For use with HY15LM grout only.

Hot weather concreting procedures, such as ACI 305 Hot Weather Concreting, must be followed.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

HYA15HT can be used in temperatures as low as 70 °F (21 °C) to extend working time; however, this may slow the compressive strength curve.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

Noord-Amerika

+1.800.753.9221

optie 1 – Klantenservice

optie 2 – Technische

ondersteuning

Europa

Nederland:

+31 800-0200135

Frankrijk:

+33 800 901 793

Europa

Duitsland:

800 1890272

andere landen:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE