

Varistar CP Seismic Base/Plinth, 103H 800W 600D

Energiebedrijven

CATALOGUSNUMMER

21630-115

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

KENMERKEN

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

PRODUCTKENMERKEN

Product Type: Cabinet/Rack Base

Product Family: Varistar CP

Type: Base Plinth

Material: Staal

Color: Black Grey

Color Code: RAL 7021

Height: 103 mm

Width: 800 mm

Depth: 800 mm

Complies With: IEC 61587-1; IEC 61587-2

Static Load: 400 N

Works With: Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE