

Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 29 U, 1400H 800W

Power Utilities

CATALOGUSNUMMER

21630-510



Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

KENMERKEN

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

PRODUCTKENMERKEN

Producttype: Kastdeur

Productfamilie: Varistar CP

Type: Stalen deur, geperforeerd

Werkt met: Varistar CP

Type vergrendeling: Vergrendeling op één punt

Kleur: Zwart grijs

Kleurcode: RAL 7021

Rekhoogte: 29 U

Hoogte: 1400 mm

Breedte: 800 mm

Beschermingsgraad: IP20

Voldoet aan: IEC 61587-1

AANVULLENDE PRODUCTGEGEVENS

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE