

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Power Utilities

Non-EMC shielded subrack for backplane mounting, light version.



CERTIFICERINGEN



KENMERKEN

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

SPECIFICATIES

Table 1/2

Catalogusnummer	Rekhoogte	Diepte	Pakkethoeveelheid	Voor montage	Diepte van de plank	Inclusief handvat
24564-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Nee
24564-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Nee
24564-431	6 U	175 mm	1	Backplane	160 mm	Nee
24564-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Nee
24564-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Nee
24564-131	3 U	175 mm	1	Backplane	160 mm	Nee

Table 2/2

Catalogusnummer	Montage	Voldoet aan	EMC-afscherming	Producttype	Rekbreedte	Statische belasting
24564-433	Rek	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nee	Subrack/chassis	84 HP	7.5 kgf
24564-432	Rek	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nee	Subrack/chassis	84 HP	7.5 kgf
24564-431	Rek	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nee	Subrack/chassis	84 HP	7.5 kgf
24564-133	Rek	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nee	Subrack/chassis	84 HP	7.5 kgf
24564-132	Rek	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nee	Subrack/chassis	84 HP	7.5 kgf
24564-131	Rek	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nee	Subrack/chassis	84 HP	7.5 kgf

AANVULLENDE PRODUCTGEGEVENS

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE