

EuropacPRO 19" Subrack Kit for Backplane, Rugged, Shielded

Energiebedrijven

Subrack with reinforced horizontal rails and side panels for backplane mounting.



CERTIFICERINGEN



KENMERKEN

Subrack with side panel and horizontal rail, type R "rugged" with 3 hole fixing for increased stability (+60% compared to 2 hole fixing of "Heavy" rails)

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip. Special adaptor rails allow conduction cooled assemblies to be fitted

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, -102, -103, IEEE 1101.1, IEEE 1101.10

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Shock and vibration tested to MIL 167, IEC 61587 DL 3, MIL 810 G, MIL 901D. Shock and vibration resistant in all three axial directions.

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available. Subrack with telescoping slides can be adopted for cabinet mounting on request

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Diepte	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24567-149	3 U	295 mm	1	Backplane	160 mm	Textile
24567-449	6 U	295 mm	1	Backplane	160 mm	Textile

Table 2/3

Catalogusnummer	Shock and Vibration Tolerance	Handle Included	Montage	Voldoet aan	EMC Shielding	Product Type
24567-149	25 g (force)	Ja	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	Ja	Subrack/Chassis
24567-449	25 g (force)	Ja	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	Ja	Subrack/Chassis

Table 3/3

Catalogusnummer	Rack Width	Statische belasting
24567-149	84 HP	25 kgf
24567-449	84 HP	25 kgf

ADDITIONAL PRODUCT DETAILS

Test reports online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE