

EuropacPRO 19" Subrack Kit for Backplane, Shielded, CompactPCI

Energiebedrijven

EMC Shielded subrack for backplane mounting, for CPCI application.

CERTIFICERINGEN



KENMERKEN

Subrack with side panel type F ("flexible") for CompactPCI plug-in units with high insertion and withdrawal forces

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, -102, -103, -104, IEEE 1101.1, IEEE 1101.10/11

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Supplied as space-saving flat-pack

IP 20, in accordance with IEC 60529

Horizontal rail type "Heavy"

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Diepte	Rear I/O	Package Quantity	For Mounting	Board Depth
24563-157	3 U	275 mm	Ja	1	Backplane	80 mm, 160 mm

Catalogusnummer	Rack Height	Diepte	Rear I/O	Package Quantity	For Mounting	Board Depth
24563-152	3 U	235 mm		1	Backplane	160 mm
24563-452	6 U	235 mm		1	Backplane	160 mm
24563-457	6 U	275 mm	Ja	1	Backplane	80 mm, 160 mm

Table 2/3

Catalogusnummer	EMC Gasket Type	Handle Included	Montage	Voldoet aan	EMC Shielding	Product Type
24563-157	Textile	Nee	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11	Ja	Subrack/Chassis
24563-152	Textile	Nee	Rack	IEC 60297-3-103, IEEE 1101.10	Ja	Subrack/Chassis
24563-452	Textile	Nee	Rack	IEC 60297-3-103, IEEE 1101.10	Ja	Subrack/Chassis
24563-457	Textile	Nee	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11	Ja	Subrack/Chassis

Table 3/3

Catalogusnummer	Rack Width	Statische belasting
24563-157	84 HP	11 kgf
24563-152	84 HP	11 kgf
24563-452	84 HP	11 kgf
24563-457	84 HP	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE