

EuropacPRO 19" Subrack Kit for Backplane, Shielded

Energiebedrijven

EMC Shielded subrack for backplane mounting, rear side covered by a rear panel.



CERTIFICERINGEN



KENMERKEN

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Aluminum construction

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "light"

SPECIFICATIES

Product Type: Subrack/Chassis

Table 1/2

Catalogusnummer	Rack Height	Diepte	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-142	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-143	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-144	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-145	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-146	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-442	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-443	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-444	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-445	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-446	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile

Table 2/2

Catalogusnummer	Handle Included	Montage	Voldoet aan	EMC Shielding	Rack Width	Statische belasting
24563-142	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-143	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-144	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-145	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf

Catalogusnummer	HandleIncluded	Montage	Voldoet aan	EMC Shielding	Rack Width	Statische belasting
24563-146	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-442	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-443	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-444	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-445	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-446	Nee	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE