

# EuropacPRO 19" Subrack Kit for Railway, Shielded, EN 50155, CompactPCI

## Power Utilities



Subrack for Railway applications, conform to EN50155 standard, for Compact PCI applications.

### CERTIFICERINGEN

---



### KENMERKEN

---

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Supplied as space-saving flat-pack

### SPECIFICATIES

---

Table 1/3

| Catalogusnummer | Rekhoogte | Pakkethoeveelheid | Voor montage | Diepte van de plank | Type pakking | Schok- en trillingstolerantie |
|-----------------|-----------|-------------------|--------------|---------------------|--------------|-------------------------------|
| 21500-082       | 6 U       | 1                 | Backplane    | 160 mm              | Textile      | 5 g (force)                   |
| 21500-081       | 3 U       | 1                 | Backplane    | 160 mm              | Textile      | 5 g (force)                   |

Table 2/3

| Catalogusnummer | Inclusief handvat | Montage | Voldoet aan                                                        | Diepte | EMC-afscherming | Producttype     |
|-----------------|-------------------|---------|--------------------------------------------------------------------|--------|-----------------|-----------------|
| 21500-082       | Ja                | Rek     | IEC 60297-3-103, IEEE 1101,10, IEEE 1101,11, EN 50155 deel 12.2.11 | 235 mm | Ja              | Subrack/chassis |
| 21500-081       | Ja                | Rek     | IEC 60297-3-103, IEEE 1101,10, IEEE 1101,11, EN 50155 deel 12.2.11 | 235 mm | Ja              | Subrack/chassis |

Table 3/3

| Catalogusnummer | Rekbreedte | Statische belasting |
|-----------------|------------|---------------------|
| 21500-082       | 84 HP      | 15 kgf              |
| 21500-081       | 84 HP      | 15 kgf              |

## AANVULLENDE PRODUCTGEGEVENS

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**