

Front Panel, Anodized With Untreated Edges, Unshielded

Energiebedrijven

Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.



CERTIFICERINGEN



KENMERKEN

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30818-271	2 U	84 HP	1	Geen	Screw-on Front	Anodized
30818-310	3 U	42 HP	1	Geen	Screw-on Front	Anodized

Catalogusnummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30818-331	3 U	63 HP	1	Geen	Screw-on Front	Anodized
30818-352	3 U	84 HP	1	Geen	Screw-on Front	Anodized
30818-434	4 U	84 HP	1	Geen	Screw-on Front	Anodized
30818-556	6 U	42 HP	1	Geen	Screw-on Front	Anodized
30818-577	6 U	63 HP	1	Geen	Screw-on Front	Anodized
30818-598	6 U	84 HP	1	Geen	Screw-on Front	Anodized
30810-433	3 U	2 HP	5	Geen	Screw-on Front	Anodized
30818-747	6 U	2 HP	5	Geen	Screw-on Front	Anodized
30818-272	3 U	3 HP	5	Geen	Screw-on Front	Anodized
30818-273	3 U	4 HP	5	Geen	Screw-on Front	Anodized
30818-274	3 U	5 HP	5	Geen	Screw-on Front	Anodized
30818-275	3 U	6 HP	5	Geen	Screw-on Front	Anodized
30818-276	3 U	7 HP	5	Geen	Screw-on Front	Anodized
30818-277	3 U	8 HP	5	Geen	Screw-on Front	Anodized
30818-279	3 U	10 HP	5	Geen	Screw-on Front	Anodized
30818-281	3 U	12 HP	5	Geen	Screw-on Front	Anodized
30818-282	3 U	14 HP	5	Geen	Screw-on Front	Anodized
30818-284	3 U	16 HP		Geen	Screw-on Front	Anodized

Catalogusnummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30818-289	3 U	21 HP	5	Geen	Screw-on Front	Anodized
30818-296	3 U	28 HP	5	Geen	Screw-on Front	Anodized
30818-517	6 U	3 HP		Geen	Screw-on Front	Anodized
30818-518	6 U	4 HP	5	Geen	Screw-on Front	Anodized
30818-519	6 U	5 HP	5	Geen	Screw-on Front	Anodized
30818-520	6 U	6 HP	5	Geen	Screw-on Front	Anodized
30818-521	6 U	7 HP	5	Geen	Screw-on Front	Anodized
30818-522	6 U	8 HP	5	Geen	Screw-on Front	Anodized
30818-524	6 U	10 HP	5	Geen	Screw-on Front	Anodized
30818-526	6 U	12 HP	5	Geen	Screw-on Front	Anodized
30818-528	6 U	14 HP	5	Geen	Screw-on Front	Anodized
30818-530	6 U	16 HP	5	Geen	Screw-on Front	Anodized
30818-535	6 U	21 HP	5	Geen	Screw-on Front	Anodized
30818-542	6 U	28 HP	5	Geen	Screw-on Front	Anodized

Table 2/3

Catalogusnummer	Rear Finish	Treated Edges	Voltoet aan	EMC Shielding	Hoogte	Materiaal
30818-271	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	84 mm	Aluminium
30818-310	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium

Catalogusnummer	Rear Finish	Treated Edges	Voldoet aan	EMC Shielding	Hoogte	Materiaal
30818-331	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-352	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-434	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	172.9 mm	Aluminium
30818-556	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-577	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-598	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30810-433	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-747	Anodized	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-272	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-273	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-274	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-275	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-276	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-277	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium

Catalogusnummer	Rear Finish	Treated Edges	Voldoet aan	EMC Shielding	Hoogte	Materiaal
30818-279	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-281	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-282	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-284	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-289	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-296	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium
30818-517	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-518	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-519	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-520	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-521	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-522	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-524	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-526	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium

Catalogusnummer	Rear Finish	Treated Edges	Voldoet aan	EMC Shielding	Hoogte	Materiaal
30818-528	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-530	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-535	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium
30818-542	Anodized	Nee	IEC 60297-3-101, IEEE 1101.1/10	Nee	261.8 mm	Aluminium

Table 3/3

Catalogusnummer	Product Type	Type	Breedte	Certificeringen
30818-271	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-310	Front Panel	Front Panel without Handle	213 mm	RoHS
30818-331	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30818-352	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-434	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-556	Front Panel	Front Panel without Handle	213 mm	RoHS
30818-577	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30818-598	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30810-433	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30818-747	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30818-272	Front Panel	Front Panel without Handle	14.9 mm	RoHS
30818-273	Front Panel	Front Panel without Handle	20 mm	RoHS

Catalogusnummer	Product Type	Type	Breedte	Certificeringen
30818-274	Front Panel	Front Panel without Handle	25 mm	RoHS
30818-275	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30818-276	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30818-277	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30818-279	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30818-281	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30818-282	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30818-284	Front Panel	Front Panel without Handle	80.9 mm	
30818-289	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30818-296	Front Panel	Front Panel without Handle	141.9 mm	RoHS
30818-517	Front Panel	Front Panel without Handle	14.9 mm	
30818-518	Front Panel	Front Panel without Handle	20 mm	RoHS
30818-519	Front Panel	Front Panel without Handle	25 mm	RoHS
30818-520	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30818-521	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30818-522	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30818-524	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30818-526	Front Panel	Front Panel without Handle	60.6 mm	RoHS

Catalogusnummer	Product Type	Type	Breedte	Certificeringen
30818-528	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30818-530	Front Panel	Front Panel without Handle	80.9 mm	RoHS
30818-535	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30818-542	Front Panel	Front Panel without Handle	141.9 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE