

Front Panel, Flat, With Slot for Stainless Steel EMC Gasket

Energiebedrijven

Front panel, flat, with slot for stainless steel EMC gasket.

CERTIFICERINGEN



KENMERKEN

Flat front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For stainless steel gasket

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish	Treated Edges
30846-682	63 HP	1	Screw-on Front			
30846-681	42 HP	1	Screw-on Front	Anodized	Conductive	Nee

Table 2/2

Catalogusnummer	Hoogte	Materiaal	Product Type	Rack Height	Type	Breedte
30846-682	172.9 mm	Aluminium	Front Panel	4 U	Front Panel without Handle	319.7 mm
30846-681	172.9 mm	Aluminium	Front Panel	4 U	Front Panel without Handle	213 mm

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE