

# Front Panel, Unshielded, With Fastener Pin

## Energiebedrijven



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

### CERTIFICERINGEN



### KENMERKEN

Enable grounding of the front area (protection class 1)

### SPECIFICATIES

| Table 1/3       |            |                  |                |              |             |               |
|-----------------|------------|------------------|----------------|--------------|-------------|---------------|
| Catalogusnummer | Rack Width | Package Quantity | Montage        | Front Finish | Rear Finish | Treated Edges |
| 20119-159       | 7 HP       | 1                | Screw-on Front | Anodized     | Conductive  | Nee           |
| 20119-160       | 14 HP      | 1                | Screw-on Front | Anodized     | Conductive  | Nee           |
| 20119-161       | 21 HP      | 1                | Screw-on Front | Anodized     | Conductive  | Nee           |
| 20119-162       | 28 HP      | 1                | Screw-on Front | Anodized     | Conductive  | Nee           |

| Catalogusnummer | Rack Width | Package Quantity | Montage        | Front Finish | Rear Finish | Treated Edges |
|-----------------|------------|------------------|----------------|--------------|-------------|---------------|
| 20119-163       | 42 HP      | 1                | Screw-on Front | Anodized     | Anodized    | Nee           |

Table 2/3

| Catalogusnummer | Voltoet aan                     | EMC Shielding | Hoogte   | Materiaal | Product Type | Rack Height |
|-----------------|---------------------------------|---------------|----------|-----------|--------------|-------------|
| 20119-159       | IEC 60297-3-101, IEEE 1101.1/10 | Nee           | 128.4 mm | Aluminium | Front Panel  | 3 U         |
| 20119-160       | IEC 60297-3-101, IEEE 1101.1/10 | Nee           | 128.4 mm | Aluminium | Front Panel  | 3 U         |
| 20119-161       | IEC 60297-3-101, IEEE 1101.1/10 | Nee           | 128.4 mm | Aluminium | Front Panel  | 3 U         |
| 20119-162       | IEC 60297-3-101, IEEE 1101.1/10 | Nee           | 128.4 mm | Aluminium | Front Panel  | 3 U         |
| 20119-163       | IEC 60297-3-101, IEEE 1101.1/10 | Nee           | 128.4 mm | Aluminium | Front Panel  | 3 U         |

Table 3/3

| Catalogusnummer | Type                       | Breedte  |
|-----------------|----------------------------|----------|
| 20119-159       | Front Panel without Handle | 35.2 mm  |
| 20119-160       | Front Panel without Handle | 70.8 mm  |
| 20119-161       | Front Panel without Handle | 106.3 mm |
| 20119-162       | Front Panel without Handle | 141.9 mm |
| 20119-163       | Front Panel without Handle | 213 mm   |

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WAARSCHUWING

---

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van [www.nvent.com](http://www.nvent.com) of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRachte**