

MultipacPRO 19" Chassis, Aluminum, Plain Top and Base

Energiebedrijven



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

CERTIFICERINGEN



KENMERKEN

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Diepte	Usable Width	Montage	Voldoet aan	EMC Shielding
20860-601	1 U	220 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-602	1 U	280 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-603	1 U	340 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-604	2 U	220 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-605	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-606	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-607	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-608	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-609	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-610	3 U	460 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-611	4 U	280 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-612	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-613	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-614	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-615	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2

Catalogusnummer	Product Family	Product Type	Type	Certificeringen
20860-601	MultipacPRO	Subrack/Chassis	Massief	RoHS

Catalogusnummer	Product Family	Product Type	Type	Certificeringen
20860-602	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-603	MultipacPRO	Subrack/Chassis	Massief	
20860-604	MultipacPRO	Subrack/Chassis	Massief	
20860-605	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-606	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-607	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-608	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-609	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-610	MultipacPRO	Subrack/Chassis	Massief	
20860-611	MultipacPRO	Subrack/Chassis	Massief	
20860-612	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-613	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-614	MultipacPRO	Subrack/Chassis	Massief	RoHS
20860-615	MultipacPRO	Subrack/Chassis	Massief	RoHS

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE