

Novastar Cabinet With Glazed Door and Rear Panel

Energiebedrijven



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFICERINGEN



KENMERKEN

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Frame Color	Hoogte	Frame Color Code	Cladding Material	Breedte
-----------------	-------------	-------------	--------	------------------	-------------------	---------

15230-019	12 U	Black Grey	589 mm	RAL 7021	Staal	553 mm
16230-019	12 U	Black Grey	589 mm	RAL 7021	Staal	553 mm
15230-020	16 U	Black Grey	767 mm	RAL 7021	Staal	553 mm
16230-020	16 U	Black Grey	767 mm	RAL 7021	Staal	553 mm
15230-021	20 U	Black Grey	945 mm	RAL 7021	Staal	553 mm
16230-021	20 U	Black Grey	945 mm	RAL 7021	Staal	553 mm
15230-022	38 U	Black Grey	1745 mm	RAL 7021	Staal	553 mm
15230-023	38 U	Black Grey	1745 mm	RAL 7021	Staal	553 mm
16230-022	38 U	Black Grey	1745 mm	RAL 7021	Staal	553 mm
16230-023	38 U	Black Grey	1745 mm	RAL 7021	Staal	553 mm
15230-024	43 U	Black Grey	1967 mm	RAL 7021	Staal	553 mm
15230-025	43 U	Black Grey	1967 mm	RAL 7021	Staal	553 mm
16230-024	43 U	Black Grey	1967 mm	RAL 7021	Staal	553 mm
16230-025	43 U	Black Grey	1967 mm	RAL 7021	Staal	553 mm

Table 2/3

Catalogusnummer	Cladding Color	Diepte	Statische belasting	Cladding Color Code	Volddoet aan	Frame Material
15230-019	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-019	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-020	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium

Catalogusnummer	Cladding Color	Diepte	Statische belasting	Cladding Color Code	Volddoet aan	Frame Material
16230-020	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-021	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-021	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-022	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
15230-023	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-022	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
16230-023	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-024	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
15230-025	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-024	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
16230-025	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium

Table 3/3

Catalogusnummer	Product Type	Protection Rating
15230-019	Cabinet	IP20
16230-019	Cabinet	IP20
15230-020	Cabinet	IP20
16230-020	Cabinet	IP20
15230-021	Cabinet	IP20
16230-021	Cabinet	IP20

Catalogusnummer	Product Type	Protection Rating
15230-022	Cabinet	IP20
15230-023	Cabinet	IP20
16230-022	Cabinet	IP20
16230-023	Cabinet	IP20
15230-024	Cabinet	IP20
15230-025	Cabinet	IP20
16230-024	Cabinet	IP20
16230-025	Cabinet	IP20

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE