

PBC gevlochten stroomgeleider

Energiebedrijven



CERTIFICERINGEN



KENMERKEN

Ideal for transformer-busduct link

Solid palms can be drilled to fit customer specific designs

Extra flexible power connection and good resistance to vibration

SPECIFICATIES

Table 1/2

Catalogusnummer	Artikelnummer	ΔT 30 K	ΔT 50 K	A	B	C
PBC100X250	564000	349 A	462 A	35 mm	40 mm	7 mm

Table 2/2


Catalogusnummer	Artikelnummer	2 Bar Current Coefficient
-----------------	---------------	---------------------------

PBC100X250	564000	1.72
------------	--------	------

ADDITIONAL PRODUCT DETAILS

When used in parallel, the two shunts must be spaced with a minimum distance equal to the thickness of the shunt to allow air cooling.

DIAGRAMMEN



WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE