

RackPower PDU, RP1xxx, 230/400 VAC, 3-phase

Energiebedrijven

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

KENMERKEN

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6" with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

SPECIFICATIES

Table 1/2

Catalogusnummer	Product Type	Socket Type	Kleur	Lengte	Voltage AC	Function
RP1450	Socket Strip	IEC C13, IEC C13/C19	Zwart	1490 mm	230 V	Input Monitored
RP1850	Socket Strip	IEC C13, IEC C13/C19	Zwart	1780 mm	230 V	Input Monitored
RP1950	Socket Strip	IEC C13, IEC C13/C19	Zwart	1826 mm	230 V	Input Monitored

Table 2/2

Catalogusnummer	Diepte	Breedte
RP1450	55 mm	56 mm
RP1850	55 mm	56 mm
RP1950	75 mm	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE