

Varistar CP Bottom Rear Panel, Shortened

Energiebedrijven

Shortened Rear Panel available for IP20, IP55 and EMC applications.

Shortened rear panels ensure efficient cable management.

KENMERKEN

Screw fixed, Robust and Single person mountable Side Panel

Plain or with brush strip

Height of connection plate 400 mm

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Hoogte	Breedte	Protection Rating	Kleur	Color Code
21630-354	38 U	1800 mm	600 mm	IP55	Black Grey	RAL 7021
21630-355	38 U	1800 mm	800 mm	IP55	Black Grey	RAL 7021
21630-356	42 U	2000 mm	600 mm	IP55	Black Grey	RAL 7021
21630-357	42 U	2000 mm	800 mm	IP55	Black Grey	RAL 7021
21630-358	47 U	2200 mm	600 mm	IP55	Black Grey	RAL 7021
21630-359	47 U	2200 mm	800 mm	IP55	Black Grey	RAL 7021

Table 2/2

Catalogusnummer	Product Type
21630-354	Cabinet Door

Catalogusnummer	Product Type
21630-355	Cabinet Door
21630-356	Cabinet Door
21630-357	Cabinet Door
21630-358	Cabinet Door
21630-359	Cabinet Door

ADDITIONAL PRODUCT DETAILS

The height of the rear panel is 400 mm less than the cabinet height to accomodate the connecting plate.

Please purchase the grounding kit separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE