

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

Energiebedrijven

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

KENMERKEN

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Hoogte	Frame Color	Breedte	Frame Color Code	Cladding Material
10630-034	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Staal
10630-033	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Staal
10630-035	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Staal
10630-036	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Staal

Table 2/3

Catalogusnummer	Diepte	Cladding Color	Cladding Color Code	Voldoet aan	Frame Material	Product Type
-----------------	--------	----------------	---------------------	-------------	----------------	--------------

10630-034	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Staal	Cabinet
10630-033	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Staal	Cabinet
10630-035	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Staal	Cabinet
10630-036	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Staal	Cabinet

Table 3/3

Catalogusnummer	Statische belasting
10630-034	400 kgf
10630-033	400 kgf
10630-035	400 kgf
10630-036	400 kgf

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE