

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Energiebedrijven

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

KENMERKEN

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Hoogte	Breedte	Kleur	Color Code	Voldoet aan
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Catalogusnummer	Afwerking	Locking Type	Materiaal	Product Type	Protection Rating	Type
21630-820	Gepoedercoat	3-Point Locking, Electronic	Staal	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Gepoedercoat	3-Point Locking, Electronic	Staal	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Gepoedercoat	3-Point Locking, Electronic	Staal	Cabinet Door	IP20	Steel Double Door, Perforated
21630-823	Gepoedercoat	3-Point Locking, Electronic	Staal	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Gepoedercoat	3-Point Locking, Electronic	Staal	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Gepoedercoat	3-Point Locking, Electronic	Staal	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Catalogusnummer	Works With
21630-820	Varistar CP
21630-821	Varistar CP
21630-822	Varistar CP
21630-823	Varistar CP
21630-824	Varistar CP
21630-825	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE