

Varistar CP Steel Door, Perforated With Multi-Point Locking

Energiebedrijven

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

KENMERKEN

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Hoogte	Breedte	Kleur	Color Code	Locking Type
21630-533	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-534	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-535	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-536	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-537	33 U	1600 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-538	33 U	1600 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-539	38 U	1800 mm	600 mm	Black Grey	RAL 7021	4-Point Locking

Catalogusnummer	Rack Height	Hoogte	Breedte	Kleur	Color Code	Locking Type
21630-540	38 U	1800 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-541	42 U	2000 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-542	42 U	2000 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-543	47 U	2200 mm	600 mm	Black Grey	RAL 7021	5-Point Locking
21630-544	47 U	2200 mm	800 mm	Black Grey	RAL 7021	5-Point Locking

Table 2/2

Catalogusnummer	Materiaal	Product Type	Type
21630-533	Staal	Cabinet Door	Steel Door, Perforated
21630-534	Staal	Cabinet Door	Steel Door, Perforated
21630-535	Staal	Cabinet Door	Steel Door, Perforated
21630-536	Staal	Cabinet Door	Steel Door, Perforated
21630-537	Staal	Cabinet Door	Steel Door, Perforated
21630-538	Staal	Cabinet Door	Steel Door, Perforated
21630-539	Staal	Cabinet Door	Steel Door, Perforated
21630-540	Staal	Cabinet Door	Steel Door, Perforated
21630-541	Staal	Cabinet Door	Steel Door, Perforated
21630-542	Staal	Cabinet Door	Steel Door, Perforated
21630-543	Staal	Cabinet Door	Steel Door, Perforated
21630-544	Staal	Cabinet Door	Steel Door, Perforated

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE