

ElectroMelt Self-Regulating Heating Cable



nVent RAYCHEM ElectroMelt EM2-XR is a rugged and robust self-regulating heating cable used to prevent snow and ice formation on ramps, loading bays, external stairs and access ways. Power output is 90 W/m at 0 °C.

KENMERKEN

Simple to design

Robust and easy to install: cable is resistant to damage during installation, cut to length

Safe and efficient in operation: no overheating, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIES

Table 1/2

Catalogusnummer	Naam van het item	Supply Voltage	Nominal Power Output @ 0°C, 230V	Outer Jacket Material	Max Circuit Length	Kleur
449561-000	EM2-XR	208 – 277 V	90 W/m	Modified Polyolefin	85 m	Oranje

Table 2/2

Catalogusnummer	Naam van het item	Nominal Width	Nominal Thickness	Ground Path Type	Minimale installatietemperatuur
449561-000	EM2-XR	18.9 mm	9.5 mm	Braid	-18 °C

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere

handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT