

FrostGuard Self-Regulating Cable Kit



nVent RAYCHEM FrostGuard kits contain self regulating trace heating cables, pre-installed with electrical cable and plug to provide an energy-efficient and easy-to-use solution for pipe freeze protection.

KENMERKEN

Simple to design: kit format, available in 17 sizes

Easy to install: small and flexible trace heating cable, pre-installed with a plug and cold lead to avoid the need for connection by an electrician, ideal for small diameter pipework and condensate pipework of condensing boilers

Energy efficient and safe: self-regulating cable, no overheating possible even when overlapped or closely spaced

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIES

Cold Lead Length:	2 m
Nominal Height:	5,8 mm
Nominal Width:	8,5 mm
Nominal Power Output @ 5°C, 230V:	10 W/m
Max Continuous Exposure Temperature, Power Off:	65 °C
Nominale spanning:	230 V
Minimale installatietemperatuur:	-5 °C
Kleur:	Zwart
Ground Path Type:	Braid
Outer Jacket Material:	Fluorpolymeer
Heating Cable Technology:	Self-Regulating

Table 1/1

Catalogusnummer	Naam van het item	Nominal Power Output, In-Pipe @ 230V	Lengte
1244-022826	FROSTGUARD-30M	16 W/m	30 m

Catalogusnummer	Naam van het item	Nominal Power Output, In-Pipe @ 230V	Lengte
1244-022827	FROSTGUARD-35M	16 W/m	35 m
1244-022828	FROSTGUARD-40M	16 W/m	40 m
1244-022829	FROSTGUARD-50M	16 W/m	50 m
1244-022830	FROSTGUARD-60M	16 W/m	60 m
1244-022831	FROSTGUARD-80M		80 m
1244-022832	FROSTGUARD-100M		100 m
107442-000	FROSTGUARD-22M	16 W/m	22 m
108722-000	FROSTGUARD-13M	16 W/m	13 m
468683-000	FROSTGUARD-19M	16 W/m	19 m
493074-000	FROSTGUARD-8M	16 W/m	8 m
524628-000	FROSTGUARD-4M	16 W/m	4 m
641438-000	FROSTGUARD-10M	16 W/m	10 m
768868-000	FROSTGUARD-25M	16 W/m	25 m
845612-000	FROSTGUARD-6M	16 W/m	6 m
924248-000	FROSTGUARD-16M	16 W/m	16 m
928206-000	FROSTGUARD-2M	16 W/m	2 m

ADDITIONAL PRODUCT DETAILS

Subject to local norms and approvals, FrostGuard can be used for in-pipe applications. For in-pipe applications (where permitted) install using a nVent RAYCHEM approved pipe entry gland assembly.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT