

MONI-PT100-4/20MA Sensor Assembly for Hazardous Areas



nVent RAYCHEM MONI-PT100-4/20MA is a PT100 sensor connected to a 4-20 mA transmitter built into a black glass fiber reinforced polyester junction box. Suitable for hazardous areas.

KENMERKEN

Simple and fast to install: built in a black glass fiber reinforced polyester junction box with blue M20 cable gland

Temperature measuring range: -50 °C to +250 °C

SPECIFICATIES

Table 1/2

Catalogusnummer	Naam van het item	Housing Material	Montage	Max Measuring Range	Bedrijfstemperatuur	Fixed Cable to Sensor
704058-000	PT100-4/20MA	Glass Fibre Reinforced Polyester	Bracket	250 °C	-20 to 55 °C	Ja

Table 2/2

Catalogusnummer	Naam van het item	Lengte kabel	Sensor Tip Diameter
704058-000	PT100-4/20MA	2 m	3 mm

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT