

NGC-40 Series, Power Distribution and Supply Panel

nVent RAYCHEM NGC-40 Panel Solution is a multipoint electronic control, monitoring and power distribution system with a unique single-point controller architecture, providing the most reliable central control and monitoring solution for your heat management system. Supporting up to 32 circuits per panel, the system offers fully flexible configuration and individual single-phase and three-phase controllers with SIL2 safety temperature limiters. System status and faults are reported to the user, displayed on the nVent RAYCHEM Touch 1500 user interface or remotely using nVent RAYCHEM Supervisor software.

KENMERKEN

Easy to install, configure and operate

Extensive control, monitoring, alarm and power distribution capabilities

Modular, providing configuration and component flexibility: optimizing project specific needs and costs

Comprehensive communications, system status and faults are reported with messages and alarms: optimizing maintenance and recovery time

SPECIFICATIES

Main Switch Current Rating: 160 A

Voltage Rating: 240 V

Table 1/1

Catalogusnummer	Naam van het item	Circuit Breaker Quantity	Circuit Breaker	Control Module	Touch 1500 Included
1244-014353	PSS-160A/10KA-PDS-40-12HTC/25A-2HTC3/40A	14	25 A, Type C	12 x NGC-40-HTC, 2 x NGC-40-HTC3	Nee
1244-014352	PSS-160A/10kA-PDS-40-12HTC/25A-2HTC3/40A-T	14	25 A, Type C	12 x NGC-40-HTC, 2 x NGC-40-HTC3	Ja

Catalogusnummer	Naam van het item	Circuit Breaker Quantity	Circuit Breaker	Control Module	Touch 1500 Included
1244-014348	PSS-160A/10KA-PDS-40-24HTC/16A-T	24	16 A, Type C	24 x NGC-40-HTC	Ja
1244-014350	PSS-160A/10KA-PDS-40-30HTC/16A-T	30	16 A, Type C	30 x NGC-40-HTC	Ja
1244-014351	PSS-160A/10KA-PDS-40-30HTC/16A	30	16 A, Type C	30 x NGC-40-HTC	Nee
1244-014349	PSS-160A/10KA-PDS-40-24HTC/16A	24	16 A, Type C	24 x NGC-40-HTC	Nee

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT