

SBS-XX-EV Control Panel for Roof and Gutter De-Icing

nVent RAYCHEM SBS-XX-EV-10 control panel provides an integrated solution for nVent RAYCHEM self-regulating heating cables in roof and gutter de-icing applications. It offers multi-circuits, multi-sensor, and multi-control with integrated electrical protection. Driven by the built-in smart nVent RAYCHEM EMDR-10 control device, it allows the system only to be activated when cold weather and moisture are detected in combination. A 400 VAC (3 phase) supply is required.

KENMERKEN

Simple and fast connection of multiple circuits, directly into a single panel

High capacity, with 3-12 maximum circuit lengths connected into the panel

Fully integrated system: all connections, circuit protection and safety devices integrated into the panel

Energy saving: through built-in EMDR-10 smart controller, circuits energized only when cold weather and moisture are detected

Reliable, complete system from one manufacturer and specifically designed for roof and gutter de-icing systems

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIES

IP-classificatie: IP65

Housing Material: Staal

Montage: Wall Mounted

Table 1/2

Catalogusnummer	Naam van het item	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA	Hoogte
295014-000	SBS-03-EV-10	3	20 A, Type C	32 A	1	600 mm
458484-000	SBS-06-EV-10	6	20 A, Type C	63 A	2	600 mm
282458-000	SBS-12-EV-10	12	20 A, Type C	100 A	4	800 mm

Catalogusnummer	Naam van het item	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30mA	Hoogte
206336-000	SBS-09-EV-10	9	20 A, Type C	63 A	3	600 mm

Table 2/2

Catalogusnummer	Naam van het item	Breedte	Diepte
295014-000	SBS-03-EV-10	400 mm	210 mm
458484-000	SBS-06-EV-10	600 mm	210 mm
282458-000	SBS-12-EV-10	800 mm	210 mm
206336-000	SBS-09-EV-10	600 mm	210 mm

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT