

AT-TS Surface Sensing Thermostat



nVent RAYCHEM AT-TS Thermostats are electronic line or ambient sensing thermostats for self-regulating heating cables in pipe freeze protection or temperature maintenance applications.

KENMERKEN

Energy saving, line-sensing or ambient electronic control thermostat.

Adjustable: -5 °C to +15 °C (AT-TS-13), 0 °C to +120 °C (AT-TS-14)

Direct switching of heating cables, maximum current 16 A, 250 VAC

Simple and fast to install

Easy to use: LEDs indicate when cables are energized or when temperature sensor is defective

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIES

Diepte:	55 mm
Hoogte:	120 mm
Breedte:	122 mm
IP-classificatie:	IP65

Table 1/1

Catalogusnummer	Naam van het item	Temperature Control Range
648945-000	AT-TS-14	0 – 120 °C
728129-000	AT-TS-13	-5 to 15 °C

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of

opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT