

# TT3000 Conductive Liquids Sensing Cable, Modular



nVent RAYCHEM TraceTek TT3000-XX-MC are a range of fixed length modular leak detection cables with metal connectors, used to detect spills and leaks of conductive liquids, including waste water, acids, bases and hazardous waste streams. Installed with an alarm and locating module, the cable senses aqueous chemical leaks, triggers an alarm and pinpoints the location. The cable is designed for a variety of applications, including floor surfaces, subfloors, equipment locations, pipes, storage tanks, and trenches.

## KENMERKEN

Advanced technology: conductive polymer & fluoropolymer construction, mechanically strong and resistant to chemicals

Simple and fast to install: small, lightweight and flexible

Easy to design

Distributed leak detection and location over a wide range of areas

Reliable and durable: 5 year product warranty available

## SPECIFICATIES

|                                   |                                          |
|-----------------------------------|------------------------------------------|
| <b>Buitenste diameter:</b>        | 6 mm                                     |
| <b>Max Operating Temperature:</b> | 85 °C                                    |
| <b>Detection:</b>                 | Conductive Liquids and Aqueous Chemicals |
| <b>Detection Method:</b>          | Raychem Conductive-Polymer Technology    |
| <b>Model:</b>                     | Sensing Cable                            |

Table 1/1

| Catalogusnummer | Naam van het item   | Lengte |
|-----------------|---------------------|--------|
| 148983-000      | TT3000-0.3M/1FT-MC  | 0.3 m  |
| 301795-000      | TT3000-30M/100FT-MC | 30 m   |
| 262789-000      | TT3000-1.5M/5FT-MC  | 1.5 m  |

| Catalogusnummer | Naam van het item   | Lengte |
|-----------------|---------------------|--------|
| 492017-000      | TT3000-60M/200FT-MC | 60 m   |
| 048179-000      | TT3000-15M/50FT-MC  | 15 m   |
| 103619-000      | TT3000-7.5M/25FT-MC | 7.5 m  |
| 792293-000      | TT3000-4.5M/15FT-MC | 4.5 m  |
| 842667-000      | TT3000-3M/10FT-MC   | 3 m    |

## WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van [www.nvent.com](http://www.nvent.com) of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

### Noord-Amerika

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latijns-Amerika

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**