

Universal Connection Kit for PI Cables



nVent RAYCHEM CS -150-UNI-PI is a universal under-insulation cold applied connection kit for polymer insulated (PI) heating cables, for splicing and connection of PI heating cables to cold leads (max 32A) or 3-core flexible power cables (max 25A) using screw terminals. Approved for use in hazardous areas.

KENMERKEN

Simple and fast to install

Different configurations, tailored to each application

Electrical connections made via terminal block, no special tools required

Approved for use in hazardous areas

SPECIFICATIES

Table 1/2

Catalogusnummer	Naam van het item	Aansluiting type	Voltage Rating	Current Rating	Max Operating Temperature	IP-classificatie
A45371-000	CS-150-UNI-PI	Cold Applied	750 V max	32 A	180 °C	IP66

Table 2/2

Catalogusnummer	Naam van het item	Area Classification
A45371-000	CS-150-UNI-PI	Non-Hazardous, Hazardous

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT