

XL-Trace Contractor Pack, Low Smoke Zero Halogen Self-Regulating Cable Kit



nVent RAYCHEM contractor packs comprise a fixed length of heating cable supplied in an easy-to-use and carry spool box. The spool allows the installer to feed out the required length easily, reducing installation time and effort.

KENMERKEN

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Zero halogen: IEC60754-1 tested and compliant

Improved self-extinguishing properties under the IEC62395 flammability test

Energy efficient: self-regulating cable, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible

Self-regulating technology: cut-to-length on site to mitigate any design variations

Quick and easy installation with the RayClic fast connection system

SPECIFICATIES

Nominal Height:	6,8 mm
Nominal Width:	13,8 mm
Supply Voltage:	220 – 240 V
Minimale installatietemperatuur:	-40 °C
Ground Path Type:	Braid
Outer Jacket Material:	Low Smoke Zero Halogen
Heating Cable Technology:	Self-Regulating

Table 1/1

Catalogusnummer	Naam van het item	Lengte	Nominal Power Output @ 5°C, 230V	Max Continuous Exposure Temperature, Power On	Kleur
1244-021262	XL-Trace-InstallerPack-10XL-30m	30 m	10 W/m	65 °C	Plum
1244-021263	XL-Trace-InstallerPack-10XL-50m	50 m	10 W/m	65 °C	Plum
1244-021264	XL-Trace-InstallerPack-10XL-80m	80 m	10 W/m	65 °C	Plum
1244-021265	XL-Trace-InstallerPack-15XL-50m	50 m	15 W/m	65 °C	Groen
1244-021266	XL-Trace-InstallerPack-15XL-80m	80 m	15 W/m	65 °C	Groen
1244-021267	XL-Trace-InstallerPack-26XL-50m	50 m	26 W/m	65 °C	Blauw
1244-021268	XL-Trace-InstallerPack-26XL-80m	80 m	26 W/m	65 °C	Blauw
1244-021269	XL-Trace-InstallerPack-31XL-50m	50 m	31 W/m	85 °C	Paars
1244-021270	XL-Trace-InstallerPack-31XL-80m	80 m	31 W/m	85 °C	Paars

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT