

XL-Trace Low Smoke Zero Halogen Self-Regulating Heating Cable



nVent RAYCHEM XL-Trace self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection and flow maintenance in grease waste lines. Developed with low smoke zero halogen (LSZH) materials, to ensure the safest solution for modern building design.

KENMERKEN

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Simple to design: long circuit lengths to 215 m, for fewer power connections and faster installation

Easy to install: highly flexible cable, cut to length, meter marks, fast RayClic cold connection system

Energy efficient and safe: self-regulating cable, advanced energy saving controls, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible, low smoke zero halogen

Reliable during long life: 10 year product warranty available, UV resistant, colorfast, maintenance free

SPECIFICATIES

Nominal Thickness:	6,8 mm
Nominal Width:	13,8 mm
Supply Voltage:	220 – 240 V
Minimale installatietemperatuur:	-40 °C
Ground Path Type:	Braid
Outer Jacket Material:	Low Smoke Zero Halogen
Geleidermateriaal:	Nickel-Plated Copper

Table 1/1

Catalogusnummer	Naam van het item	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Kleur
P000002113	10XL2-ZH	10 W/m	238 m	Plum

Catalogusnummer	Naam van het item	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Kleur
P000002114	15XL2-ZH	15 W/m	188 m	Groen
P000002115	26XL2-ZH	26 W/m	142 m	Blauw
P000002116	31XL2-ZH	31 W/m	114 m	Paars

ADDITIONAL PRODUCT DETAILS

Circuit Lengths are based on a 20 A C-Type characteristic circuit protection device, Power on at +5 °C.

When selecting the heating circuit length, the maximum switching capacity of the respective controller must be taken into account.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT