

# XL-Trace Pre-Terminated, Low Smoke Zero Halogen Self-Regulating Cable Kit



nVent RAYCHEM kits comprise a 10XL2-ZH self-regulating heating cable with a pre-installed low smoke zero halogen cold lead cable of 4 m, cold lead to heater cable splice and end seal. The kits are available in fixed lengths between 3-30 m. Factory terminated and electrically tested.

## KENMERKEN

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Energy efficient: self-regulating cable, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible

Easy to install, pre-terminated kits

Zero halogen: IEC60754-1 tested and compliant

Improved self-extinguishing properties under the IEC62395 flammability test

## SPECIFICATIES

|                                                       |                        |
|-------------------------------------------------------|------------------------|
| <b>Cold Lead Length:</b>                              | 4 m                    |
| <b>Nominal Height:</b>                                | 6,8 mm                 |
| <b>Nominal Power Output @ 5°C, 230V:</b>              | 10 W/m                 |
| <b>Nominal Width:</b>                                 | 13,8 mm                |
| <b>Max Continuous Exposure Temperature, Power On:</b> | 65 °C                  |
| <b>Supply Voltage:</b>                                | 220 – 240 V            |
| <b>Minimale installatietemperatuur:</b>               | -40 °C                 |
| <b>Ground Path Type:</b>                              | Braid                  |
| <b>Outer Jacket Material:</b>                         | Low Smoke Zero Halogen |
| <b>Kleur:</b>                                         | Plum                   |
| <b>Heating Cable Technology:</b>                      | Self-Regulating        |

Table 1/1

| Catalogusnummer | Naam van het item | Lengte |
|-----------------|-------------------|--------|
| 1244-021271     | 10XL2-ZH-KIT-3m   | 3 m    |
| 1244-021272     | 10XL2-ZH-KIT-5m   | 5 m    |
| 1244-021273     | 10XL2-ZH-KIT-8m   | 8 m    |
| 1244-021274     | 10XL2-ZH-KIT-12m  | 12 m   |
| 1244-021275     | 10XL2-ZH-KIT-16m  | 16 m   |
| 1244-021276     | 10XL2-ZH-KIT-20m  | 20 m   |
| 1244-021277     | 10XL2-ZH-KIT-25m  | 25 m   |
| 1244-021278     | 10XL2-ZH-KIT-30m  | 30 m   |

## WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van [www.nvent.com](http://www.nvent.com) of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

### Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**