

PSU 19" for CompactPCI, AC/DC, 3 U, 300 W

CATALOGUSNUMMER

13100-143



Pluggable 19" Power Supply with P47 connector, for CompactPCI applications.

KENMERKEN

Connector P47 and CompactPCI signalling

4 output voltages

Redundant operation with Current Share Bus (CSB), hot-swap

PRODUCTKENMERKEN

Producttype: Voeding

Type: 19 inch geschakelde modus

Werkt met: CompactPCI-systemen; VME64x-systemen

Ingangsspanning AC: 90 – 264V

Voeding: 300W

Aantal uitgangsspanningen: 4

Spanning 1: 5V

Stroom 1: 40A

Spanning 2: 3.3V

Stroom 2: 40A

Spanning 3: 12V

Stroom 3: 10A

Spanning 4: -12V

Stroom 4: 2A

Rekhoogte: 3U

Rekbreedte: 8HP

Hoeveelheid in verpakking: 1

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE