

CPCI Serial R3.0 System With Pluggable PSU, 4 U, 9 Slot, With Rear I/O

CATALOGUSNUMMER

24579-451



4 U CompactPCI Serial R3.0 System, with vertical Card Cage for nine 3 U Boards and one 3U Pluggable Power Supply.

KENMERKEN

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG CPCI-S.0 R3.0

Supports PCIe Gen 4, 10 Gbase-T, S-ATA 3 and USB 3.2 Gen 2

Ethernet interface is 10GBASE-KR and 10GBASE-T capable and 25GBASE-KR ready

System with vertical card cage. For Board format 3U

Backplane 9 slot, 3U CompactPCI Serial (single star Ethernet topology), System slot left

Heat dissipation via 1 U hot-swap fan unit

Retrofittable air filter

PRODUCTKENMERKEN

Producttype: Systeem

Aantal sleuven: 9

Type: 19 inch rekmontage

Type achterzijde: 3 U CompactPCI Serial met Ethernet Star

Gegevensoverdracht: PCIe Gen4

Vermogen per sleuf: 40W

Ingangsspanning AC: 100 – 240V

Luchtstroomrichting: Onder naar boven

Rekhoogte: 4U

Type voeding: (2) Insteekbare voeding

Voeding inbegrepen: Ja

I/O achter: Ja

Voldoet aan: PICMG CPCI-S.0 R3.0

Diepte: 275mm

Hoogte: 177mm

Rekbreedte: 84HP

Sleufbreedte: 4HP

Systeemslot: Links

AANVULLENDE PRODUCTGEGEVENS

Preference types can be ordered directly from stock, other configurations on request.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE