

EuropacPRO 19" Subrack Kit for Railway, Shielded, EN 50155



Subrack for Railway applications, conform to EN50155 standard, shielded versions.

CERTIFICERINGEN



KENMERKEN

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

SPECIFICATIES

Statische belasting:	15kg
Rekbreedte:	84HP
Diepte:	235mm
Materiaal:	Aluminium
Voldoet aan:	IEC 60297-3-103; EN 50155 deel 12.2.11

Producttype: Subrack/chassis

EMC-afscherming: Ja

Table 1/2

Catalogusnummer	Rekhoogte	Hoeveelheid in verpakking	Voor montage	Diepte plaat	Type EMC-pakking	Tolerantie voor schokken en trillingen
21500-079	3U	1	Achterplaat	220mm	Textiel	5g (force)
21500-080	6U	1	Achterplaat	220mm	Textiel	5g (force)

Table 2/2

Catalogusnummer	Handgreep inbegrepen	Montage	Afwerking	Snelle verzending
21500-079	Ja	Rek	Geanodiseerd, Geëloxeerd	Nee
21500-080	Ja	Rek	Geanodiseerd, Geëloxeerd	Nee

AANVULLENDE PRODUCTGEGEVENS

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE