

Rack Safety Plus, 3 U, 208 / 240 V AC



KENMERKEN

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

208 V phase to phase or phase to neutral or 240 V phase to phase mains input

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

UL pending

SPECIFICATIES

Functie:	Noodstop
Inschakelstroombegrenzer:	Nee
Aardlekschakelaar:	Nee
Afdekking van de stroomonderbreker:	Nee
Werkt met:	Varistar CP; Novastar
Type accessoire:	Accessoires voor stroomverdeling

Table 1/2

Catalogusnummer	Producttype	Ingangsspanning AC	Aantal fasen	EMC-filter	Overspanningsbeveiliger	Rekhoogte
21272-003	Stroomverdeler	208 – 240V	1	Nee	Nee	3U
21272-001	Stroomverdeler	208 – 240V	1	Ja	Ja	3U

Table 2/2

Catalogusnummer	Type fitting	Hoeveelheid in verpakking	Snelle verzending
21272-003	IEC C13 lockable	1	Nee
21272-001	IEC C13, IEC C19	1	Nee

AANVULLENDE PRODUCTGEGEVENS

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE