

Telescopic Slide, Universal, Heavy Load, 2 U



Telescopic slides with 10 to 100 kg load capacity, > 100% extension length and with lateral mounting capability on 19". Robust telescopic sliding-rails - suitable for the installation of 19 inch chassis are suitable for mounting server enclosures from our product portfolio. Due to the extremely robust construction and high load capacity, the telescopic slides can also be used with very heavy housings.

CERTIFICERINGEN



KENMERKEN

Static load-carrying capacity per pair 72 - 100 kg

Lateral mounting on the 19" uprights (19" plane remains free for fixing the extension/drawer)

End stop damped

Extension length > 100 %

Rail width k = 19.1 mm, max. installation width of extension/drawer w = 411 mm

SPECIFICATIES

- Materiaal:** Staal
Producttype: Telescopische schuif
Afwerking: Verzinkt

Table 1/1

Catalogusnummer	Lengte	Hoeveelheid in verpakking	Statische belasting	Type	Snelle verzending
20110-190	300mm	2	77kg	Universeel	Nee

Catalogusnummer	Lengte	Hoeveelheid in verpakking	Statische belasting	Type	Snelle verzending
20110-193	450mm	2	94kg	Universeel	Nee
20110-192	400mm	2	88kg	Universeel	Nee
20110-194	500mm	2	100kg	Universeel	Nee
20110-195	550mm	2	94kg	Universeel	Nee
20110-191	350mm	2	83kg	Universeel	Nee
20110-196	600mm	2	88kg	Universeel	Nee
20110-198	700mm	2	72kg	Universeel	Nee

AANVULLENDE PRODUCTGEGEVENS

To mount on 19" plane please order assembly kit separately.

Universal telescopic rails can also be fitted without additional components in non-standard applications, thus also in other than 19" cabinets.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE