

## CS480 zwenkvoet inwendig



CS480 Swivel Base Internal allows the entire suspension system to rotate at the point of attachment on a horizontal surface. Arm can be rotated or turned 340 degrees. Base mounting hardware is hidden. Maintenance-free bearings.

### INDUSTRIENORMEN

---

IEC 60529, IP66

### KENMERKEN

---

Base can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket is included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

## SPECIFICATIES

| Table 1/1       |        |         |        |                     |            |                   |
|-----------------|--------|---------|--------|---------------------|------------|-------------------|
| Catalogusnummer | Hoogte | Breedte | Diepte | Materiaal           | Voltooien  | Snelle verzending |
| CCSS48BBRI      | 110mm  | 116mm   | 116mm  | Roestvrij staal 304 | Geborsteld | Nee               |

## WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**