

CS480 u-vormige boogarm



CS480 U-Shaped Pendant Tube is pre-cut and shaped with two 90-degree bends to reduce assembly time. For use in conjunction with CS480 Stainless Steel Pendant Arm system components.

INDUSTRIENORMEN

IEC 60529, IP66

KENMERKEN

Use of these tubes does not compromise the enclosure rating

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFICATIES

Afwerking: Gepolijst
Materiaal: Roestvrij staal 304

Table 1/1

Catalogusnummer	Hoogte	Breedte	Diepte	Dikte	Snelle verzending
CCSSTU802480	800mm	240mm	800mm	3.6mm	Nee
CCSSTU502450	500mm	240mm	500mm	3.6mm	Nee

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE