

Main busbar supports horizontal | Stroomverdeling, MSHS



This horizontal busbar support, MSHS, for two bars up to 120x10 mm, is available off the shelf and has been tested according to IEC 61439. It can be mounted at any height behind fix, modular, and plug-in systems.

KENMERKEN

Omschrijving: Busbar supports up to 3600A to be mounted horizontally behind the compartments. Mounts to the internal side panels MSPS, and in the height position which we need. Supports for single or double bar per phase for bar thickness 10 mm, and width from 10 to 120 mm. Distance between bars of 20 mm.

Materiaal: Polycarbonate reinforced with 10% of glass material.

Levering: Busbar support for 3 phases and neutral, and mounting material.

Distance between bars of 20 mm

Material: Polycarbonate reinforced with 10% of glass material

Delivery: Busbar support for 3 phases and neutral, and mounting material

Horizontal main busbar support for 2 bars up to 120 x 10 mm, which can be mounted at the required height behind any system (fix, modular or plug-in)

The standard supports are available off the shelf and have been tested according to IEC 61439

The supports are suitable for the most common bars on the market

Main busbars can be installed in the middle of the enclosure height, which will reduce the required busbar section

A flexible and reliable solution that ensures procurement, design and installation can be done efficiently reducing the labour time required

Internal side panels (MSPS) are required in order to mount the busbar supports

SPECIFICATIES

Table 1/1						
Catalogusnummer	Hoogte	Breedte	Materiaal behuizing	Productserie	Materiaal	Afwerking
MSHS408010	620mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad
MSHS401010	300mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad
MSHS405010	540mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad
MSHS406010	540mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad
MSHS403010	420mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad
MSHS410010	700mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad
MSHS404010	460mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad
MSHS412010	780mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad
MSHS402010	380mm	95mm	Plaatstaal	Vrijstaand	Polycarbonaat	Glad

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE