

Verticale paneelkoppeling, licht, S1MPCV



Suspend 180-Max Vertical Panel Coupling mounts a vertical tube to the back of an enclosure or screen using Video Electronics Standards Association (VESA) mounting. The coupling has mounting holes drilled for standard VESA 75 and 100 flange sizes. It enables the enclosure to rotate 300 degrees and can be locked into a given position. The vertical panel coupling has a safety stop and maintenance-free bearings.

KENMERKEN

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

White aluminum cable access cap is included

Assembled Suspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

SPECIFICATIES

Materiaal: Aluminium
Afwerking: Gepoedercoat

Table 1/1

Catalogusnummer	Hoogte	Breedte	Diepte	Kleur	Kleurcode	Dikte
S1MPCVG	185mm	120mm	140mm	Lichtgrijs	RAL 7035	5.5mm
S1MPCV	256mm	140mm	120mm	Gitzwart	RAL 9005	5.5mm

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE