

CPP Tapered Plastic Screw-In Plug for A12, A22 and A32K, 28 mm, #9, 30M

CATALOGUSNUMMER

EL28CPPB100



KENMERKEN

Designed for use with the A12, A22 and A32K coupler families

Designed to keep dirt, water and concrete slurry out of the coupler during the concrete pour

Color coded for the appropriate coupler size

PRODUCTKENMERKEN

Artikelnummer: 153140

Materiaal: Hoge dichtheid polyethyleen (HDPE)

Grootte rebar, metrisch: 28 mm

Formaat wapening, VS: #9


Formaat rebar, Canada: 30M

Diameter (Ø): 37 mm

Hoogte (H): 16 mm

Kleur: Zwart

Pakkethoeveelheid: 100



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

Noord-Amerika

+1.800.753.9221
optie 1 – Klantenservice
optie 2 – Technische
ondersteuning

Europa

Nederland:
+31 800-0200135
Frankrijk:
+33 800 901 793

Europa

Duitsland:
800 1890272
andere landen:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE