

nVent LENTON inspectiesleutel



nVent LENTON taper-threaded couplers are typically installed with a standard pipe wrench. The nVent LENTON inspection wrench is provided to check tightness of connections. The frequency of inspection is set by the governing building codes or inspector.

When installing nVent LENTON taper-threaded products, refer to the specific nVent LENTON Product Instruction Sheets and/or Governing Building Codes and Approvals for the proper wrench setting. The specified torque value is easily set using the scale attached to the wrench.

KENMERKEN

All wrenches are marked with unique serial numbers

Setting of torque values is simple

Used on multiple bar sizes

SPECIFICATIES

Table 1/2

Catalogusnummer	Artikelnummer	Wapeningsmaat, metrisch	Wapeningsmaat, VS	Wapeningsmaat, Canada	Lengte 1 (L1)	Lengte 2 (L2)
148010	148010	10 - 28 mm	#3 – #9	10M – 30M	630 mm	60 mm Max
148030	148030	20 - 57 mm	#6 – #18	20M – 55M	825 mm	80 mm Max

Table 2/2

Catalogusnummer	Artikelnummer	Hoogte 1 (H1)	Hoogte 2 (H2)	Gewicht eenheid
148010	148010	75mm	40mm	2.5 kg
148030	148030	90mm	45mm	3.7 kg

AANVULLENDE PRODUCTGEGEVENS


To ensure safety, good footing and/or balance should be maintained when using wrenches of this type. Failure to maintain footing or balance could result in injury and/or damage to property. Note further product safety instructions in safety documentation provided with the wrench.

Follow manufacturer's recommendation for recalibration of the wrench. Typically, service and re-calibration are required once a year.

Ensure that the tool is stored properly to minimize damage. When stored for long periods, adjust the tool to a low setting to relieve stress on internal parts.

For further information, please review the manufacturer's instructions.

DIAGRAMMEN



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

Noord-Amerika

+1.800.753.9221

optie 1 – Klantenservice

optie 2 – Technische

ondersteuning

Europa

Nederland:

+31 800-0200135

Frankrijk:

+33 800 901 793

Europa

Duitsland:

800 1890272

andere landen:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE