

19" Fan Unit, 1 U, Speed Control and Monitoring

Energiebedrijven

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICERINGEN



KENMERKEN

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPECIFICATIES

Table 1/1

Catalogusnummer	Input Voltage AC	Input Voltage DC	Certificeringen
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Catalogusnummer	Input Voltage AC	Input Voltage DC	Certificeringen
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE