

19" Pusher Fan, 2 U, Axial

Energiebedrijven

Fan tray with integrated pusher fan.



CERTIFICERINGEN



KENMERKEN

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to subracks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

SPECIFICATIES

Table 1/1

Catalogusnummer	Input Voltage AC	Input Voltage DC
10713-518	230 V min	
10713-520	115 V min	

Catalogusnummer	Input Voltage AC	Input Voltage DC
10713-526	230 V min	
10713-534	230 V min	
10713-536	115 V min	
10713-529		24 V min
10713-537		24 V min
19713-540		

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE