

Assembly Parts for Rugged Components

Energiebedrijven



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

CERTIFICERINGEN



KENMERKEN

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

SPECIFICATIES

Table 1/2

Catalogusnummer	Type	Lengte	Package Quantity	Formaat draad	Materiaal	Product Family
24566-105	Countersunk Screw	7 mm	100	M4	Roestvrij staal	EuropacPRO
24566-104	Panhead Screw	8 mm	100	M4	Roestvrij staal	EuropacPRO
24566-103	Panhead Screw	10 mm	100	M4	Roestvrij staal	EuropacPRO
24566-106	Countersunk Screw	10 mm	100	M4	Roestvrij staal	EuropacPRO

Catalogusnummer	Type	Lengte	Package Quantity	Formaat draad	Materiaal	Product Family
24566-101	Countersunk Screw	14 mm	100	M4	Roestvrij staal	EuropacPRO
24566-102	Panhead Screw	14 mm	100	M4	Roestvrij staal	EuropacPRO
24566-100	Countersunk Screw	18 mm	100	M4	Roestvrij staal	EuropacPRO
24560-140	Square Nut		100		Roestvrij staal	EuropacPRO

Table 2/2

Catalogusnummer	Product Type	Works With
24566-105	Assembly Kit	Subracks
24566-104	Assembly Kit	Subracks
24566-103	Assembly Kit	Subracks
24566-106	Assembly Kit	Subracks
24566-101	Assembly Kit	Subracks
24566-102	Assembly Kit	Subracks
24566-100	Assembly Kit	Subracks
24560-140	Assembly Kit	Subracks

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE