

Combined Mounting Kit for Chassis

Energiebedrijven



The combined mounting enable the option to split a 6 U high subrack or case in 2 x 3 U and 6 U sections. Different versions are available.

CERTIFICERINGEN



KENMERKEN

Designed to accept Euroboards (100 mm high) and double Euroboards (233.35 mm high)

Subdivision of the 6 U assembly area into: 2 x 3 U, 1 x 6 U

SPECIFICATIES

Table 1/2

Catalogusnummer	Package Quantity	Rack Width 1	Rack Width 2	Product Family	Product Type	Rack Height
24562-484	1	84 HP		EuropacPRO	Mounting Kit	6 U
24562-420	1	20 HP	62 HP	EuropacPRO	Mounting Kit	6 U
24562-440	1	40 HP	42 HP	EuropacPRO	Mounting Kit	6 U
24562-442	1	42 HP	40 HP	EuropacPRO	Mounting Kit	6 U

Catalogusnummer	Package Quantity	Rack Width 1	Rack Width 2	Product Family	Product Type	Rack Height
24562-463	1	63 HP	19 HP	EuropacPRO	Mounting Kit	6 U

Table 2/2

Catalogusnummer	Type	Works With
24562-484	Combined	Subracks
24562-420	Combined	Subracks
24562-440	Combined	Subracks
24562-442	Combined	Subracks
24562-463	Combined	Subracks

ADDITIONAL PRODUCT DETAILS

Please order separately: Front panel 6 U, 2 HP to cover the strut.

The following guide rails cannot be used: type "accessory", type "accessory, strengthened" and type "for 4.4" PCB".

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE