

# Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

## Power Utilities

### CATALOGUSNUMMER

**34566-284**



Combinations of horizontal rails and side panels

|               | Light r.d. | Standard r.d. | Heavy r.d. | Rugged r.d. |
|---------------|------------|---------------|------------|-------------|
| Standard r.d. | -          | +             | +          | +           |
| Heavy r.d.    | +          | +             | +          | +           |
| Light r.d.    | +          | +             | -          | -           |
| Standard r.d. | +          | +             | -          | -           |

Legend: + can be combined, - combination not recommended

The rugged horizontal rail type can handle shock and vibration up to 25 g.

### CERTIFICERINGEN



### KENMERKEN

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

### PRODUCTKENMERKEN

Producttype: Horizontale rail

Productfamilie: EuropacPRO

Type: Robuust, KD

Rekbreedte: 84 HP

Lengte: 431.8 mm

## AANVULLENDE PRODUCTGEGEVENS

---

Without M4 thread to front, without printing and without notch for 19" bracket.

## WAARSCHUWING

---

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**