

Modular Single Door, MCS, 1800x500x500mm, Light Gray, Mild Steel

Energiebedrijven

CATALOGUSNUMMER

MCS18055R5



The mild steel single door modular floor standing enclosure range, MCS, with a IP 55 protection degree, is available off the shelf in many different sizes. This enclosure range is well suited for many different applications. The risk for component failure, and with that unnecessary downtime, is eliminated as water and dust are prevented from entering the enclosure.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E92044

cUL Listed per CSA C22.2 No.0, No.0.4, No.14, No.94; Type 12; File No. E92044

NEMA/EEMAC Type 12

CSA, File No. 1442951: Type 12

IEC 62208 IP55

KEMA, GOST, DNV, CE, EAC

KENMERKEN

Frame: Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660 Including integrated external hole pattern

Door: Mounted with four hinges allowing left or right hand opening; including door frame with 25 mm hole pattern

Rear panel: Fitted by M6 torx screws; standard facilities for rear door mounting

Side Panels supplied as an accessory

Removable roof panel

Lock: Espagnolette 4-point locking system which does not interfere with the enclosure inner space; standard double-bit lock with 3 mm insert

Bottom plate: Consists of three or four (D>600) pieces

Mounting plate: Double folded and slides into position with adjustable depths of 25 mm, with the MPD02 accessory

Earthing/Grounding: All panels are earthed through their fittings and are equipped with a separate earthing stud

Mounting requirements: Standard delivery ready for combined installation; for stand-alone installation add side panels

Delivery: Frame with fitted door, rear panel, roof panel, bottom plates, mounting plate (not included for PER5 version) and door frame; for 400 mm wide enclosures, a mounting plate, bottom plates and door frame are not included; for enclosures 2200 mm height, delivery includes two CMB profiles mounted in depth; delivery also includes earthing bolts

PRODUCTKENMERKEN

Article Number: MCS18055R5

Height: 1800 mm

Width: 500 mm

Depth: 500 mm

Protection Rating: NEMA Type 12; IP55; IK10

Material: Mild Steel

Finish: Gepoedercoat

Color: Light Gray

Color Code: RAL 7035

Body Thickness: 1,5 mm

Door Thickness: 2 mm

ADDITIONAL PRODUCT DETAILS

Mild steel side panels, SPM, need to be ordered separately, to close individual enclosures and enclosure assembly's, to ensure the stated protection degree is achieved.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE