

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Energiebedrijven

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFICERINGEN



KENMERKEN

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Diepte	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24567-161	3 U	175 mm	1	Backplane	160 mm	Roestvrij staal
24567-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Roestvrij staal
24567-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Roestvrij staal
24567-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal
24567-461	6 U	175 mm	1	Backplane	160 mm	Roestvrij staal
24567-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Roestvrij staal
24567-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Roestvrij staal
24567-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal

Table 2/3

Catalogusnummer	Shock and Vibration Tolerance	Handle Included	Montage	Voldoet aan	EMC Shielding	Product Type
24567-161	5 g (force)	Ja	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24567-162	5 g (force)	Ja	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24567-163	5 g (force)	Ja	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24567-164	5 g (force)	Ja	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24567-461	5 g (force)	Ja	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24567-462	5 g (force)	Ja	Rack	IEC 60297-3-103	Nee	Subrack/Chassis

Catalogusnummer	Shock and Vibration Tolerance	HandleIncluded	Montage	Voldoet aan	EMC Shielding	Product Type
24567-463	5 g (force)	Ja	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24567-464	5 g (force)	Ja	Rack	IEC 60297-3-103	Nee	Subrack/Chassis

Table 3/3

Catalogusnummer	Rack Width	Statische belasting	Certificeringen
24567-161	84 HP	15 kgf	RoHS
24567-162	84 HP	15 kgf	RoHS, DB
24567-163	84 HP	15 kgf	RoHS, DB
24567-164	84 HP	15 kgf	RoHS, DB
24567-461	84 HP	15 kgf	RoHS, DB
24567-462	84 HP	15 kgf	RoHS, DB
24567-463	84 HP	15 kgf	RoHS, DB
24567-464	84 HP	15 kgf	RoHS, DB

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE