

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding

Energiebedrijven

Rear horizontal rail for backplane mounting with insulation strip



CERTIFICERINGEN



KENMERKEN

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version without front handles

Supplied as space-saving flat-pack

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Diepte	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-161	3 U	175 mm	1	Backplane	160 mm	Textile
24563-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile
24563-461	6 U	175 mm	1	Backplane	160 mm	Textile
24563-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile

Table 2/3

Catalogusnummer	Shock and Vibration Tolerance	Handle Included	Montage	Voldoet aan	EMC Shielding	Product Type
24563-161	5 g (force)	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24563-162	5 g (force)	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24563-163	5 g (force)	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24563-164	5 g (force)	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24563-461	5 g (force)	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24563-462	5 g (force)	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis
24563-463	5 g (force)	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis

Catalogusnummer	Shock and Vibration Tolerance	HandleIncluded	Montage	Voldoet aan	EMC Shielding	Product Type
24563-464	5 g (force)	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis

Table 3/3

Catalogusnummer	Rack Width	Statische belasting
24563-161	84 HP	15 kgf
24563-162	84 HP	15 kgf
24563-163	84 HP	15 kgf
24563-164	84 HP	15 kgf
24563-461	84 HP	15 kgf
24563-462	84 HP	15 kgf
24563-463	84 HP	15 kgf
24563-464	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE