

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Energiebedrijven

Non-shielded subrack for backplane mounting.



CERTIFICERINGEN



KENMERKEN

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Diepte	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-131	3 U	175 mm	1	Backplane	160 mm	Roestvrij staal
24563-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Roestvrij staal
24563-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Roestvrij staal
24563-134	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal
24563-135	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal
24563-136	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal
24563-431	6 U	175 mm	1	Backplane	160 mm	Roestvrij staal
24563-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Roestvrij staal
24563-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Roestvrij staal
24563-434	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal
24563-435	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal
24563-436	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal

Table 2/3

Catalogusnummer	Handle Included	Montage	Voldoet aan	EMC Shielding	Product Type	Rack Width
24563-131	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-132	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP

Catalogusnummer	HandleIncluded	Montage	Volddoet aan	EMC Shielding	Product Type	Rack Width
24563-133	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-134	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-135	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-136	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-431	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-432	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-433	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-434	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-435	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-436	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP

Table 3/3

Catalogusnummer	Statische belasting
24563-131	11 kgf
24563-132	11 kgf
24563-133	11 kgf
24563-134	11 kgf
24563-135	11 kgf
24563-136	11 kgf
24563-431	11 kgf

Catalogusnummer	Statische belasting
24563-432	11 kgf
24563-433	11 kgf
24563-434	11 kgf
24563-435	11 kgf
24563-436	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE